


SMART LIFTING SYSTEMS

LL12 – 20m Technical Document





Product



LUXLIFT 12/20m

Short name	LL - 12/20m	Cable Light Circuit	3x1,0mm ²
Lifting weight	0- 12kg	Cable auxiliary contacts	4x0,75mm ²
Power Motor	30w	Current auxiliary contacts	max. 6A
Power connection Motor/Light	separate	Protection category	IP54
Lowering distance	0-20m	Protection class	1
Current draw standby	0,08 A	Temperature range	-15°C to 60°C
Power supply Motor	100- 264V/50-60Hz	Net weight	6.4kg
Power supply Light	100- 264V/50-60Hz	Speed	ca. 3 - 3.5m/min
Current Light Circuit	max. 10A	Dimensions	230x230x230mm

Components

Safety Locking Device



The Safety locking device provides additional security when the lift is at rest.

Special safety locking jaws engage to take the load off the suspension cables.

The jaws remain locked even in the event of a power failure and only disengage when the lift is operated.

Electrical Contact Plates



Electrical contact is made by way of spring loaded contacts plates within the main unit and fixed contacts in the lowering coupler of the lift.

Upon lowering the lift the internal relay isolates the electrical supply, once in the raised position the relay returns power to the lower contacts











Dimensions












Mounting Points

Standard Mounting Points




Upper attachment:

Make sure that the selected mounting plate has a load capacity that corresponds to the combined weight of the lift and the towed object.

To comply with EU regulations ensure that LuxLift is connected to the ceiling with at least two independent attachment points.

M6

max. screw depth 13 mm



Lower attachment:

Make sure that the selected mounting plate allows the towed object to be suspended so that the center of gravity is centrally located below the lift plate.

M6

max. screw depth 11 mm

Wiring Diagram

Connection Cable

All lifts have 4 connection cables.



Motor:

BLUE = neutral conductor BROWN = Phase YELLOW/GREEN = protective earth

One connection is marked "MOTOR" and ensures the power supply to the lift motor.

A 5 A fuse must be provided in the building installation.

Potential free control cable Motor Light down / up N L PE N L PE C1 C2 C3 C4 4 x 0.75 mm² 3 x 1.0 mm²

Light:

BLUE = neutral conductor BROWN = Phase YELLOW/GREEN = protective earth

The connection "LIGHT" supplies the lift control and also leads via the contact plates to teh load plate of the lift and is used there to supply the light.

A 10 A fuse must be provided in the building installation.

Auxiliary contacts:

4 conductors: Black, Grey, Brown and Blue

The auxiliary contacts (C1-C4) can be used for DALI, DMX, emergency luminaires or other applications.




In the normal state (lighting operation and public traffic), it must be ensured that te motor circuit is de-energised and cannot be switched on without authorisation.



Functions


Auto Stop Feature

When lowering, the lift stops automatically if the decent is interrupted or when it reaches the ground.



Adjustable Lowering Height

Each lift can be set to stop at the users desired lowering height. This can be stored in the lift for future operations.



Group Mode Feature

Lifts can be grouped into four units to allow rasie and lowering of raft and grid systems.



Sync Mode Feature

Lifts can be grouped into pairs to lower and raise linear truss and banner applications.



Keyswitch

Keyswitch

Control cables:


3 conductors - Black, White and Red


These are used to connect the lift to the wired control system. (Optional; in case no remote control tablet is used) **External voltage must not be applied to the control lines of the lift under any circumstances,** as this will cause the lift to fail.


Control switch



Do not connect Black+Red+White Do not connect any voltage







Mobile App

Control via the app

Control of the LuxLift

- Saving the lowering distances
- Setting up synchronous groups
- Manual control

Lift information management

- Installation date
- Personalize lift name
- Store room information
- Photo of the lift or a floorplan

Monitoring Functions

- Status of the luminaire (switched on / off)
- Last cleaning/maintenance of the luminaire
- Operating hours counter
 - Last bulb replacement



Accessories

Top Mounting Plate (MP-O-25)

The ingenious shape of the upper mounting plate enables uncomplicated lift assembly:

- The mouting plate is screwed to the top of the lift with the four screws included in the scope of delivery.
- Two screws are attached to the ceiling at a distance of 223mm. (Celiing mounting hardware with the lift is not included).
- Then the mounting plate together with the lift is hung in the ceiling screws and screwed tight.

Material: aluminium - Thickness 3mm



Upper Mounting Plate with Eyebolt (MP-OE-25)

The upper mounting plate with eyebolt is suitable for LuxLift Light 12 and LuxLift Light 25 and is made of 3mm thick aluminium. It is suitable as a ceiling mounting plate with a suspension point in the centre of gravity.

the top mounting plate with eyebolt comes with four bolts for attachment to the lift. The ring nu is already pre-installed and glued to the mounting plate. Ceiling mounting hardward is not included.





Bottom Mounting Plate (MP-UE-75)

The lower mounting plate allows you to mount your lights or objects from a single point using a ring nut, as well as attaching mounting brackets using prefabricated screw holes.

The scope of delivery includes:

- M8 ring bolt with associated self-locking nut
- Four spacer sleeves and associated M6 screws for fastening the mounting plate to the Luxlift.

Colour: White (RAL-9016)









Accessories continued...

Inspection Cover with Four Screws (RA-MSS)

The inspection cover closes the installation opening in suspended ceilings and hides the view of the lift.

Material: Aluminium Thickness: 2.5mm Diameter: 400mm

Standard Colour: White (RAL-9016),

custom colour possible.





Inspection Cover with Ring Screw (RA-ME)

The inspection cover closes the installation opening in suspended ceilings and hides the view of the lift. The attachment of the object to be attached to the lift is carried out with an eyebolt and a self-locking nut, which are included in the scope of delivery.

Material: Aluminium Thickness: 2.5mm Diameter: 400mm

Standard Colour: White (RAL-9016),

custom colour possible.





www.luxlift.co.uk info@luxlift.co.uk